

WP-GT BRASS M12 - Protective hose screw connection



3241031

<https://www.phoenixcontact.com/gb/products/3241031>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland made from brass with metric thread, rotatable, IP40 protection

Commercial data

Item number	3241031
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AF7DSA
Product key	AF7DSA
Catalog page	Page 599 (C-3-2019)
GTIN	4046356711678
Weight per piece (including packing)	21.63 g
Weight per piece (excluding packing)	21.63 g
Customs tariff number	74122000
Country of origin	DE

WP-GT BRASS M12 - Protective hose screw connection



3241031

<https://www.phoenixcontact.com/gb/products/3241031>

Technical data

Product properties

Product type	Protective hose screw connection
Type	Outer thread
Cable outlet	straight
Thread type	metric

Dimensions

Width	21 mm
Height	33 mm
Length	33 mm
Wrench size	19 mm
Wrench size for mounting	19 mm

External dimensions

Outside diameter	14 mm
------------------	-------

Internal dimensions

Internal diameter	8.5 mm
-------------------	--------

Material specifications

Color	brass color
Material	Brass, nickel-plated
Components	halogen-free

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP40
Ambient temperature (operation)	-40 °C ... 250 °C

WP-GT BRASS M12 - Protective hose screw connection



3241031

<https://www.phoenixcontact.com/gb/products/3241031>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3241031>



VDE approval of drawings

WP-GT BRASS M12 - Protective hose screw connection



3241031
<https://www.phoenixcontact.com/gb/products/3241031>

Classifications

ECLASS

ECLASS-13.0	27430310
-------------	----------

ETIM

ETIM 9.0	EC001180
----------	----------

UNSPSC

UNSPSC 21.0	40141700
-------------	----------

WP-GT BRASS M12 - Protective hose screw connection



3241031

<https://www.phoenixcontact.com/gb/products/3241031>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c38973ad-6d41-4d50-a9d5-05c5540db781

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk