

Orthomat®

The original fatigue fighter

Our research and knowledge in the field of 'fatigue-relief' for standing occupations continues to drive the development of our Orthomat® range. COBA Europe is regarded as one of the leading names in anti-fatigue matting, offering an unrivalled product choice. Our Orthomat® range has been specifically designed to reduce the onset of fatigue caused by prolonged standing. This durable, yet very comfortable matting is manufactured from 100% closed cell PVC foam, providing the right balance of underfoot cushioning and support, while encouraging healthy circulation. Browse our extensive selection of Orthomat® products to find the ideal anti-fatigue matting for your environment. Our Sales team is always happy to advise on the most suitable product.



Orthomat® Standard



Black



Grey



Safety

Orthomat® Standard The original fatigue fighter

- Single layer foam anti-fatigue workplace mat with textured surface.
- Ideal for light to medium use in dry environments.
- Safety version available with bright yellow borders.
- Insulates against cold concrete floors.

Technical Specification

Material:	Virgin Closed Cell PVC (Foam)
Surface Finish:	Pebble
Product Height:	9mm
Roll Length:	18.3m
Size of Safety Border:	100mm
Operating Temperature:	0°C to +60°C
Environmental Resistance:	Suitable for dry indoor environments
Typical Applications:	Production lines, assembly areas, packing stations, workbenches
Installation Method:	Loose lay
Cleaning Method:	Brush/Mop the top surface
Product Performance:	Conforms to Slip Resistance Test EN 13552 (Category R10)
Flame Retardancy:	Fire Tested to DIN 54332 (B2) part of DIN 4102
Country of Origin:	China
Guarantee:	1 year guarantee when used in a dry environment
Permanent Adhesive Recommendation:	F44
Release Adhesive Recommendation:	F41
Heavy-Duty / Wet Area Adhesive Recommendation:	F74, F81, F84

Sizes	Black	Grey	Black/Yellow	Weight
0.6m x 0.9m	AF010001	AF060001	AF010701	1.31 kg
0.9m x 1.5m	AF010002	AF060002	AF010702	3.27 kg
0.9m x 18.3m	AF010003	AF060003	AF010703	40.00 kg
0.9m x per linear metre	AF010003C	AF060003C	AF010703C	1.60 kg
1.2m x 18.3m	AF010005	-	AF010706	58.55 kg
1.2m x per linear metre	AF010005C	-	AF010706C	2.10 kg