



PW3 HOLSTER WORK TROUSERS

DESCRIPTION

Rugged trouser made from Kingsmill polyester/cotton 300g fabric with a modern fit and adjustable leg length. Packed full of features to offer superb function and performance including; top loading pre-shaped knee pad pockets, triple stitched seams, crotch gusset to reduce stress and prevent seam failure and a side leg cargo pocket. Pockets have oxford reinforcement for extra durability.

COMPOSITION

-  **Titanmill Plus: 65% Polyester, 35% Cotton, 300g**
-  **100% Polyester, 600D Oxford, PU Coated, 210g**
-  **Black 28-48**

FEATURES

- Durable polycotton fabric for high performance and maximum wearer comfort
- Reinforced panels in high wear areas for maximum durability
- Reflective piping for increased visibility
- Top-loading knee pad pockets for quick and easy access
- Swing away tool pockets
- 12 Pockets for ample storage
- 2 Side pockets
- 2 back pockets with one open and one featuring a flap
- 1 Thigh pocket with zip closure
- 1 Cargo pocket
- 1 Rule pocket
- 1 Pen pocket

STANDARDS

EN 14404: 2004 + A1: 2010 Type 2 Level 0 (When used in combination with S156)

COLOUR / SIZES

SKU	COLOUR	SIZE RANGE
T602BKR	BLACK	28-14

FEATURES



DETACHABLE ID POCKET
ID card holder for ID card display



MACHINE WASHABLE AT 60°C
Reusable and machine washable at 60 degrees



UPF 40+
40+ UPF rated fabric to block 98% of UV rays



PERFORMANCE WORKWEAR
PW3™ contemporary workwear blends sports and lifestyle trends with function, a modern fit and improved comfort.

GET THE COLLECTION



TECHINCAL INFORMATION



OEKO-TEX certification
13.HCN.29764

- Wash garment inside out
- Wash garment inside out and fully fastened
- Wash with similar colours
- Wash dark colours separately

Item	Colour Fit	Len (cm)	Wid (cm)	Hgt (cm)	Weight (Kg)	Cubic (m³)	EAN13	GTIN/DUN14
T602BKR28	Black	65	45	36	.960	5850.000	5036108291472	15036108781642
T602BKR30	Black	65	45	36	.979	5850.000	5036108289967	15036108780188
T602BKR32	Black	65	45	36	1.003	5850.000	5036108289974	15036108780195
T602BKR33	Black	65	45	36	1.050	5850.000	5036108297474	15036108787231
T602BKR34	Black	65	45	36	1.080	5850.000	5036108289981	15036108780201
T602BKR36	Black	65	45	36	1.100	5850.000	5036108289998	15036108780218
T602BKR38	Black	65	45	36	1.130	5850.000	5036108290000	15036108780225
T602BKR40	Black	65	45	36	1.073	5850.000	5036108290017	15036108780232
T602BKR41	Black	65	45	36	1.150	5850.000	5036108297481	15036108787248
T602BKR42	Black	65	45	36	1.160	5850.000	5036108290024	15036108780249
T602BKR44	Black	65	45	36	1.080	5850.000	5036108291489	15036108781659
T602BKR46	Black	65	45	36	1.180	5850.000	5036108291496	15036108781666
T602BKR48	Black	65	45	36	1.180	5850.000	5036108291502	15036108781673