

3RD ANGLE (AMERICAN) PROJECTION

DIMENSIONS IN INCHES
DIMENSIONS THUS [] IN MM

C-152656

SLEEVE

INSULATION
COLOR NATURAL
GREY

SERRATIONS

640 MAX
[16,26]

.051 MIN
[1,29]

.171^{±.003} DIA
[4,34^{±.008}]
(FOR #8 STUD)

.281 DIA
[7,14]

.242 MIN
[6,15]

.727 MAX
[18,79]

TONGUE MATERIAL
THICKNESS .031 [0,79]

FROZEN

FOR .045-.080 [1,14-2,03] WIRE IRE DIA

E 242mm length		DR	247	CUSTOMER COPY REFERENCE ONLY	
D .045-.080 [1,14-2,03]		DR	117	A DIVISION OF AMP INDUSTRIAL	
C PICTORIN CHANGE ONLY ANYL			3473	RAMPART WAY AND FACILITY MURFREET, TENN 37132	
R GREY HAD BARELY		DP	2372	RING TONGUE	
A .045/.055 HAS .045/.115		DP	22171	PIDG. TEFLON RESTRICTED SLEEVE	
DATE 26970		DE		N.T.S. E A C-152656	
CHK 8/10/79				WIRE TERMINAL ASSY	