





Matchcode	Description	Picture	Technical data	Colours
2 mm-Programme				
EPB 6053 Ni / ..(colour)	Press-in socket <ul style="list-style-type: none"> for pressing into panels up to 6 mm thick hole Ø 3.9 accessoires: mounting with press-in tool WKZ EPB2 		terminal: PIN Ø 1.5 x 8 transition resistance: 7 mΩ rated voltage: 33 VAC / 70 VDC rated current: 10 A operating temperature: -40 °C ... +90 °C	black, red, blue, yellow, green, grey, brown, white, purple
KURZ 5741 / 5.08-2 IG MB Ni / ..(colour) KURZ 5741 / 5.08-2 IG MB Au / ..(colour)	Connecting plug <ul style="list-style-type: none"> moulded insulation with rear socket Ø 2 mm 		terminal: socket transition resistance: 5 mΩ (Ni) / 3 mΩ (Au) rated voltage: 33 VAC / 70 VDC rated current: 12 A operating temperature: -40 °C ... +90 °C	black
2 mm-Safety-Programme				
SAK 6715 Ni / 2 / ..(colour)	Safety crocodile clip <ul style="list-style-type: none"> insulated socket Ø 2 mm contact: crocodile jaws grips up to Ø 8 mm 		terminal: socket transition resistance: < 15 mΩ rated voltage: 600 V CAT II rated current: 10 A operating temperature: -25 °C ... +80 °C	black, red, blue, yellow, green, white
4 mm-Programme				
EPB 6792 Ni / ..(colour)	Press-in socket <ul style="list-style-type: none"> for pressing into panels up to 6 mm thick hole Ø 6.8 accessoires: mounting with press-in tool WKZ EPB4 		terminal:FR 4.8 x 0.8 transition resistance: 4 mΩ rated voltage: 33 VAC / 70 VDC rated current: 24 A operating temperature: -40 °C ... +90 °C	black, red blue, yellow green, grey brown, white purple