



HP314

1060 Lumens | 693 m Beam | IPX4 | 4 × D

**LONG RANGE
FOCUS**
SPOT & FLOOD

High | Strobe | Low
Slide Focus

Length: 17.12" | 43.5 cm
Weight: 49.6 oz. | 1406 g
4 × D batteries included

Clam: —
Box: 19855

ANSI FL1	High	Low
Lumens	1060	150
Beam Distance	693m	261m
Runtime	2h 45min	92h



Custom EVA case with
shoulder strap and
bezel ring included



Slide Focus



Strobe

The HP314 is the ultimate torch for the serious professional as it can throw its focused beam over two-thirds of a kilometer thanks to our Long Range Focusing Optic System.

