



Main

Range	Thalassa
Product name	Thalassa PLS
Device short name	PLS
Device application	Multi-purpose
Product or component type	Insulating modular box
Enclosure nominal height	360 Mm
Enclosure nominal width	540 Mm
Enclosure nominal depth	230 Mm
Enclosure mounting	Wall mounted
Device composition	1 cover: on enclosure 1 rear part: on enclosure locking screws
Body type	One piece moulded
Type of front cover	High plain cover
Lock type	Slot screw

Complementary

Removable parts	Cover locking screw
Material	Cover: polycarbonate Rear: polyester reinforced with fibreglass
Colour	Body: grey (RAL 7035)
Standards	NEMA 4X NEMA classification 13 IEC 62208
Product certifications	UL

Environment

Electrical insulation class	Class II
IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK09 conforming to IEC 62262
Fire resistance	960 °C conforming to IEC 62208
Ambient air temperature for storage	-30...70 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	4.102 Kg
Package 1 Height	25 Cm
Package 1 width	56 Cm
Package 1 Length	38 Cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**