

LED lamp with switch, clip mounting, 100-240 V AC/DC 50/60 Hz



Model		
product brand name	SIVACON	
product designation	LED light	
design of the product	Switch with clip fixing	
type of light source	LED not replaceable	
General technical data		
consumed active power of the light source	5 W	
type of voltage of the operating voltage	AC	
Protection class		
protection class IP	IP20	
Product details		
product component		
• ON/OFF switch		
• light sensor		
• socket outlet		
product feature magnetic	No	
Connections		
type of electrical connection for through-wiring	Plug-in connection	
Mechanical Design		
height	34 mm	
width	32 mm	
depth	34 mm	
length	351 mm	
fastening method	clip fixing	
net weight	0.2 kg	
material	plastic	
Approvals Certificates		
General Product Approval	other	Environment



[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR2200-1C>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR2200-1C>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR2200-1C

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

4/15/2025 

