


ENTE :
BODY :**IMQ****Simbolo :**
Symbol :**Riconosciuto conforme alle norme :**
In accordance to standards :EN 61810-1:1998 – EN 61810-5:1998
EN 60255-23:1996

TIPO TYPE	Corrente nominale <i>Nominal current</i> Tensione nominale <i>Nominal voltage</i>	Vita elettrica a pieno Carico in AC1 (cicli) <i>Electrical life at</i> AC1 rated load (cycles)	Portata motore <i>Motor rating</i>	Temperatura ambiente <i>Ambient</i> temperature	N. File
55.X2	10 A – 250 Vac	100.000	/	85 °C	EC294 / EC295
55.X3	10 A – 250 Vac				E9970 / E9973
55.X4	7 A – 250 Vac				EE235 / EE236

Emissione LO



Approvazione UT

Livello di
revisione nr.
11**DATA REVISIONE****24.02.2003****PAGINA NR.****3/8**