



GBC 480HS Office A3 Laminator

The GBC 480HS A3 Laminator provides a reliable and efficient solution for high volume laminating needs. Designed for professional environments, this high-speed laminating machine combines performance with ease of use. Boost productivity and reduce lamination time by 30% using GBC high-speed pouches. With a rapid 1-minute warm-up time, it laminates a 75-micron A4 sheet in just 23 seconds, making it ideal for fast-paced office tasks. The intuitive control panel offers four pouch thickness settings from 75 to 175 microns, providing flexibility for various document types. The panel also features a manual reverse button and an auto-reverse function with active jam sensing for seamless pouch removal. Additionally, the SMART status LED system provides clear visual and audible cues: red during warm-up, blue with a sound when ready, and an automatic shut-off after 15 minutes of inactivity to conserve energy. The SMART entry guide LEDs ensure straight pouch alignment to prevent jams, making every lamination perfect. Protect and preserve your important documents with speed and a smooth, professional finish every time. Black and red colour.



Attributes

- Rapid warm-up time, ready to use in just 1 minute.
- Compatible with pouches from 75 to 175 microns. Laminates ID card up to A3 sized documents.
- GBC High-Speed laminators reduce lamination time by 30% when using GBC high-speed pouches.
- Laminates an A4 document (75 mic) in just 23 seconds. Laminates 26 x A4 in 10 minutes.
- SMART status LED: glows red during warm-up and turns blue with an acoustic signal when the laminator is ready to use.
- SMART entry guide LEDs: ensure pouches feed straight through the laminator to prevent jams.
- Auto-reverse feature detects an issue and automatically reverses your pouch out of the machine.
- The control panel features an anti-jam reverse button for easy removal of misfed pouches.
- Includes a starter pack of 5x A4 pouches (75 microns).
- Conserve energy with the 15-minute auto shut-off feature, which activates after detecting inactivity.
- Low noise level <50DbA for less distractions.
- For best results use with GBC document pouches. CE certified, TUV/GS.

Specifications

Number	4410072UK
Colour	
Material	ABS Plastic
Dimensions (W x H x D)	500 x 110 x 190 mm
Laminating Speed (mm/min)	800
Temperature	133C-150C
Power Supply	220-240V AC 50/60Hz
Warm up Time (min)	1
Heating System	2 from outside heated rollers
Operation Mode	4 roller, no carrier, speed controlled
Max. Laminating Width (mm)	330
Max. Laminating Thickness (mm)	0.6
Max. Pouch Thickness (microns)	75-175
Power Consumption (W)	1400
Dimensions (with Tray) mm	500 x 110 x 190
Anti-Jam Technology	Manual reverse button / Auto reverse
Approx. lamination time (A4)	23 secs (A4 80 micron)
Photo friendly	Yes
Period of Warranty (Years)	2
Type	Pouch
Weight	3570 g
Pallet quantity	0
EAN code	5028252645607