


Description: Extremely soft, Lined in black PVC. Outer surface in top-quality yellow PVC. Knitted textile reinforcement. Perfectly circular cross-section.

Temperature: -5°C +60°C .

Application: Gardening, irrigation, construction industry - building and marine.

Advantages: Good resistance to abrasion and sudden temperature changes. Excellent weather resistance. High visibility even in very low light conditions. Operating pressure higher than ordinary garden hoses.



All data refers to performance at 18°C. Any increase of temperature, above or below, will affect the performance data.
We reserve the right to change all technical data without prior notice.

I.D. mm.	O.D. mm.	Weight gr./mtr.	Working Pressure bar	Bursting Pressure bar	Coil Length mtr.
13	18	170	10	30	25/50/100
16	22	235	10	30	25/50/100
19	25	310	8	24	25/50/100
25	32	410	8	24	25/50/100

All data refers to performance at 18°C. Any increase of temperature, above or below, will affect the performance data.
We reserve the right to change all technical data without prior notice.