



Datasheet

ENGLISH

RS PRO, 12 V dc, 6000 gcm, Brushed DC Geared Motor, Output Speed 4 rpm


Stock No: 454-0861



Specifications:

Output Speed	4 rpm		
Supply Voltage	12 V dc		
Maximum Output Torque	6000 g.cm		
DC Motor Type	Brushed		
Shaft Diameter	6mm		
Power Rating	7.98 W		
Gearhead Type	Spur		
Length	70.2mm		
Width	35mm		
Current Rating	990 mA		
Weight	170g		

rspro.com



Ratio	A	В	С
3000:1	97.2mm	70.2mm	28.4mm

Gearbox Housing material	Metal
Backlash at no-load	< 2°
Bearing at output	Sleeve bearings
Radial load (10mm from flange)	< 1 kgf
Shaft axial load	< 0.7 kgf
Shaft press fit force max	< 20 kgf
Radial play of shaft	< 0.05mm
Thrust play of shaft	< 0.35mm

Reduction	Rated tolerance	Max momentary	Efficiency
Ratio	Torque	Tolerance Torque	
1/3000	6 kgf-cm Max.	18 kgf-cm	48%

Reduction Table RPM SUPPLY VOLTAGE	4.5v	6v	9v	12v	15v
454-0861	1.5	2	3	4	5

Note: Motor speeds may vary by (+) or (-) 12.5%



