

Nitrile polymer gloves with an extended full-arm cuff for enhanced chemical resistance



- **Specialized protection:** AlphaTec® 58-008 nitrile polymer gloves offer Type A chemical protection under the new ENISO 374:2016, ensuring superior personal protection against oils, fats, greases and hydrocarbons, besides providing excellent mechanical protection
- **Enhanced features:** These safety gloves feature an extended and wide cuff, which affords increased chemical protection to the forearm and allows the wearer to don it over protective clothing
- **Improved grip:** Lozenge grip pattern on AlphaTec® 58-008 nitrile polymer gloves deliver enhanced grip performance in dry and wet conditions, besides improving dexterity and reducing hand fatigue

Industries

- Agriculture
- Automotive
- Automotive Aftermarket
- Chemical
- Food Processing
- Life Sciences
- Metal fabrication
- Oil and gas
- Recycling and Waste Disposal

Applications

- Assembly & inspection of components
- Oil, fluids and filter change
- Painting or cleaning tools or robots
- Plating, coating, sealing, painting
- Handling incoming goods
- Transferring liquids and solids
- Opening and draining pumps valves or lines
- Loading and unloading of process equipment
- Transferring liquids and solids between vessels and tanks and process equipment
- Opening furnaces draining pumps valves or lines and crackers BTX process

Key Features

- **Nitrile polymer gloves:** Excellent mechanical and chemical protection
- **Extended and wide cuff:** For full arm protection
- **Lozenge grip pattern:** Enhanced grip and dexterity

Vulcanization Chemical Accelerators

- Zinc Dibutyldithiocarbamate (ZDBC)

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.



Performance Standards

EN388: 2016



4102X

EN ISO 374-1:2016



AJKLOT

EN ISO 374-5:2016



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 58-008	Liner Material: N/A Coating Material: Nitrile	8, 9, 10	640 / 25.2	Green	• 10 pairs per bag, 1 bag per carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.