



### Application Range

Reliable bending and anti-kink protection. High strain relief. Robust. For cables with large outer diameters. High degree of protection.

### Technical Data

Material: Body: Nickel Plated Brass  
Anti-Kink Seal: CR  
O Ring: NBR

Protection Rating: IP65

Temperature Range: -20°C to +80°C

### Article List

RS Part Number	Description	Thread Size	Clamping Range (mm)	Spanner Wrench (mm)	Overall Length (mm)	Thread Length (mm)
390583	Cable gland, metal, PG7	PG7	3.5 – 5	14	50	5
390599	Cable gland, metal, PG9	PG9	5.5 – 7	17	52	6
390606	Cable gland, metal, PG11	PG11	7.5 – 9	20	56	6
390612	Cable gland, metal, PG13.5	PG13.5	9 – 11	22	62	6.5
390628	Cable gland, metal, PG16	PG16	13 – 15	24	67	7
1572102	Cable gland, metal, PG21	PG21	18 – 20	30	79	7
1572118	Cable gland, metal, PG29	PG29	21 – 23	40	91	8
1572124	Cable gland, metal, PG36	PG36	30 – 33	50	110	9
1572146	Cable gland, metal, PG42	PG42	35 – 38	57	114	10

RS Part Number	Description	Thread Size	Clamping Range (mm)	Spanner Wrench (mm)	Overall Length (mm)	Thread Length (mm)
1572152	Cable gland, metal, M16	16mm	5.5 – 7	20	50	13
1572174	Cable gland, metal, M20	20mm	7.5 – 9	22	52	13
1572180	Cable gland, metal, M20	20mm	13 – 15	24	56	13
1572196	Cable gland, metal, M25	25mm	17 – 19	30	62	13