

Technical data sheet

Article number:
924-00490

BL95

Product Group	Bootlace Ferrule
Product Family	Nylon Insulated Bootlace Terminal
Material	Copper (CU), Polyamide 6.6 (PA66)
Colour	Red (RD)
Application Range	Low Voltage
Conductor Size (mm²)	95 mm ²
Diameter (D)	18 mm
Halogen-free	Yes
Length (L)	44 mm
Length (L2)	19 mm
Length (L3)	25 mm
Max Voltage	600 V
Operating Temperature	-30 °C to +105 °C
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
Ø (D2)	14.7 mm
ROHS compliant	Yes

HF ✓

RoHS ✓