

## FEATURES

- **Durable Mild Steel Construction:** Provides strength and longevity, ensuring reliable performance in industrial environments.
- **Accommodates Up to 6 Padlocks:** Allows multiple workers to apply their locks, enhancing safety during group lockout procedures.
- **9 mm Shackle Diameter:** Compatible with a wide range of padlocks, offering flexibility in lock selection.
- **Bright Red Colour:** Enhances visibility, making it easy to identify locked-out equipment.
- **ISO 9001, ISO 14001, OHSMS 45001 Certified:** Meets international standards for quality, environmental management, and occupational health and safety.

## RS PRO 6-Lock Mild Steel Lockout Hasp

RS Stock No: 710-523



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

The RS PRO Lockout Hasp is designed to provide a secure and reliable solution for locking out equipment during maintenance or repair. Made from durable mild steel, this lockout hasp can accommodate up to six padlocks, ensuring multiple workers can lock out a single energy source safely. Its robust construction and ease of use make it an essential tool for maintaining workplace safety.

## General Specifications

Colour	Red
Number of Locks	6
Product Type	Lockout Hasp
Sub Type	Lockout Hasp

## Mechanical Specifications

Material	Mild Steel
Shackle Diameter	9 mm

## Approvals

Standards/Approvals	ISO 9001, ISO 14001, OHSMS 45001, UKAS 0043
---------------------	---