



FASTECH AG
Klettverschluss-Systeme
Zurlindenstrasse 29
CH-4133 Pratteln
Switzerland

Tel. +41 (0) 61 915 90 90
Fax +41 (0) 61 915 90 99
E-Mail info@fastech.ch
Web www.fastech.ch

Specification



Technical Data Sheet

ETK FAST-Straps ETN FAST-Strap Meter

<u>Construction Characteristics</u>	
Base material	Back to Back Cable Management
Construction	Polyamide & Polyamide Velours PA
Width	Extruded and special Laminated
Overall Thickness	Nominal $\pm 1 \%$
Hooks/cm ²	1,10 $\pm$ 0,10 mm / Hook 21C high 0,38 mm
Weight	Average 320
Possible Colours	450 $\pm$ 60 g/m ²
Hook colours	White, black, blue, red, green, yellow
	Natural. except for black and white, where the hook is black or white
<u>Usage Characteristics</u>	
Peel Strength *	Minimum 0,8 N/cm
Shear Strength *	Minimum 12,5 N/cm ²
Cycle life *	50 % loss after 500 cycles
Braking Strength *	Minimum 140 N/cm
Melting Point	+150°C
Electric conductivity	None
Washing resistance (ISO 105 sec/C03)	Good
U.V. resistance	Low
Humidity resistance	Medium
Sewn resistance	Low
Acid resistance	Medium
Shelf Life	10 Years, when stored in dark area, at temperature of 10°C to 30°C.
RoHS (Tests performed)	Conform
REACH (Tests performed)	Conform