

STOFLEX HOSE ASSEMBLIES ANTI-STATIC RUBBER PAINTING

STOFLEX anti-static rubber hose extension with PREVOST
safety quick couplers



Part number	Length (m)	Temperature min/max (°C)	Max. operating pressure (bar)	Net weight (Kg)	Profile
RAL SISB810	10.00	-15.00 / 70.00	12.00	1,96	ISO 6150B
RAL SISB1012	12.50	-15.00 / 70.00	12.00	2,85	ISO 6150B
RAL SESB810	10.00	-15.00 / 70.00	12.00	1,82	EUROPEAN
RAL SESB910	10.00	-15.00 / 70.00	12.00	2,2	EUROPEAN
RAL SESB912	12.50	-15.00 / 70.00	12.00	2,5	EUROPEAN
RAL SESB1012	12.50	-15.00 / 70.00	12.00	3,08	EUROPEAN
RAL SBSB810	10.00	-15.00 / 70.00	12.00	1,9	BRITISH
RAL SBSB1012	12.50	-15.00 / 70.00	12.00	3,1	BRITISH
RAL SCSB1012	12.50	-15.00 / 70.00	12.00	2,5	ISO 6150C

Part number	Ø int/ext (mm)
RAL SISB810	8.00 / 15.00
RAL SISB1012	10.00 / 18.00
RAL SESB810	8.00 / 15.00
RAL SESB910	9.00 / 16.00
RAL SESB912	9.00 / 16.00
RAL SESB1012	10.00 / 18.00
RAL SBSB810	8.00 / 15.00
RAL SBSB1012	10.00 / 18.00
RAL SCSB1012	10.00 / 18.00