



Cut



Medium Duty

Medium-duty industrial gloves, offering durable hand coverage with assured grip

- **Advanced defenses:** ActivArm® 97-008 protective gloves feature a DuPont™ Kevlar® layer for tough, durable protection against cuts (ANSI/ISEA 105-2024 CUT A2 and EN ISO B) and harsh abrasion (ANSI/ISEA 105-2024 and EN ABRASION LEVEL 4), making them ideal for a variety of medium-duty tasks.
- **Improved grip:** Both versatile and comfortable, these breathable work gloves' foam nitrile coating enhances grip performance in wet or dry conditions and grants them a "second skin" feel, for everyday usability
- **Enhanced features:** Thanks to a seamless knit design and reinforced ridges, ActivArm® 97-008 safety gloves offer excellent tactile sensitivity without sacrificing comfort, and feature an adjustable wrist closure with pull-tab as well as an ID nameplate



Industries

- Automotive
- Automotive Aftermarket
- Construction

Applications

- Body assembly
- General maintenance
- Engine transmission and repair
- Hydraulic repair

Key Features

- **Advanced layer of DuPont™ Kevlar®:** For lightweight yet durable work gloves
- **Foam nitrile coating:** Stronger grip and dexterity for precision tasks
- **Seamless knit design with reinforced ridges:** Comfortable work gloves

Vulcanization Chemical Accelerators

- Natural rubber proteins (in knitwrist elastic)

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance



ANSI/ISEA 105-2024



EN388: 2016



4232B

Technologies

Kevlar®

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
ActivArm® 97-008	Finishing: Palm Coated Coating Material: Foam Nitrile Liner Material: Nylon, Spandex, Kevlar® Cuff Style: Velcro®	15	8, 9, 10, 11	243-284 mm, 10-11"	12 pairs/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699