

Pole Hedge Trimmer LXT®

DUN500W

18V • 50 cm

Brushless hedge trimmer for high hedge trimming.

The brushless hedge trimmer with long shaft is very suitable for cutting tall and long hedges. The blade is articulated 115 degrees, making it easy to cut the bush tops. The blade can be folded into the transport position for a full 180 degrees.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	1000 / 1800 / 2000 min ⁻¹
Strokes per Minute (SPM)	2000 / 3600 / 4400 min ⁻¹
Length Of Blade	500 mm
Max blade opening	23,5 mm
Angle range vertical	115 °
Continuous Use 18V / 6.0 Ah Battery	60 / 90 / 190 min
Sound Power Level (L _{WA})	92 dB(A)
Sound Pressure Level (L _{pA})	81 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Hedge Trimming	4,7 / 2,5 m/s ²

User benefits

- Brushless maintenance-free and long-life motor
- The narrow design of the handle ensures excellent handling
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection system automatically shuts off power when the battery level is low
- Electric brake for maximum productivity and increased operator safety

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing