



PRODUCT-DETAILS

TG408G

Wall-mounting cabinet, Rows: 8, 1250 mm x 1050 mm x 225 mm, Grounded (Class I), IP55



概要信息	
产品型号	TG408G
产品ID	2CPX010023R9999
欧洲商品编号(EAN)	4011617100232
目录说明	Wall-mounting cabinet, Rows: 8, 1250 mm x 1050 mm x 225 mm, Grounded (Class I), IP55
详细描述	Wall-mounting cabinet, series TwinLine, empty cabinet, Expansion option: Lateral and bottom, for the internal use, with Door, class of protection I (earthed), degree of protection IP55, applicable standards: EN 61439-1, EN 61439-2, EN 61439-3, Impact strength IK08, Powder-coated, in RAL 7035, enclosure out of sheet steel, double door, door out of sheet steel, with Standard locking mechanism double bit, door opening angle 180 degree, door hinge right and left, rear wall out of sheet steel, cable entry on top via flange opening pre-cut, on bottom via flange opening pre-punched, on side via flange opening pre-punched, dimensions in mm (H x W x D): 1250 x 1050 x 225, Grid unit 8 GU, Overall height 4, panel width 4, Space units 384, pre-assembled for installation of metering-, modules, Combi-Sets, CombiLine-Module, mounting plates on EDF-/WR-mounting frame

技术参数	
标准	DIN EN 61439-3 DIN EN 61439-2

功率损耗	Δt = 20K 150.3 W Δt = 25K 198.4 W Δt = 30K 248.9 W
Number of Flange Openings	4
Number of Conduit Inlets	208
行数	8
配置类型	pre-assembled for installation of metering-, modules, Combi-Sets, CombiLine-Module, mounting plates on EDF-/WR-mounting frame
盖板类型	None
外壳类型	Wall-mounting cabinet
机箱高度	4
安装类型	Surface mounting
柜门类型	Double
表面处理	Powder-coated
壳体材料	Steel plate/plastic
外壳类型	with Notch
DIN空位模块	384
RAL Number	RAL 7035 - Light Grey
颜色	Light grey

Material Compliance

RoHS信息	2CPC100021X0201
RoHS状态	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
RoHS日期	20240903
REACH Declaration	2CPC100005X0201
REACH Information	True - contains substances > 0.1 mass percentage
REACH Date	20240902
Conflict Minerals Reporting Template (CMRT)	9AKK108468A3363
SCIP	a9384434-706f-4938-bb0f-956739599fbf Germany (DE)

环境条件

防护等级	IP55
防护等级	Grounded (Class I)

尺寸

宽度(模块化垫片数)	48
产品净宽	1050 mm
产品净高	1250 mm
产品净深	225 mm
电场宽度	4
产品净重	46.629 kg
内深 (t ₂)	170 mm
Thickness	Cabinet Plate 1 mm Door Plate 1.5 mm
尺寸图	2CPC000022D0201

订货信息	
1级包装单元	pack 1 piece
1级包装 总重	48.504 kg
E-Number (Norway)	2407881

认证及声明（文件编码）	
符合性声明 - CE	2CPC100021X0201

Installation	
说明书和手册	2CPC016708M5601 2CPC119660M5601

Popular Downloads	
数据手册，技术资料	2CPC000001C0101 2CPC000002C0101
Building Information Modeling – BIM	9AKK107046A8223

分类	
ETIM 8	EC000058 - Empty cabinet
ETIM 9	EC000058 - Empty cabinet
WEEE 类别	Product Not in WEEE Scope
CN8	85381000
e级	V11.0 : 27142408
对象分类代码	U

Accessories				
Identifier	Description	Type	Quantity	Unit Of Measure
2CPX010450R9999	Flange, 147 mm x 223 mm x 20 mm	TZ101	1	piece
2CPX010452R9999	Flange, 147 mm x 223 mm x 20 mm	TZ102	1	piece
2CPX010454R9999	Flange, 147 mm x 223 mm x 20 mm	TZ103	1	piece
2CPX010456R9999	Flange, 147 mm x 223 mm x 20 mm	TZ104	1	piece
2CPX010457R9999	Flange, 147 mm x 223 mm x 20 mm	TZ105	1	piece
2CPX010458R9999	Flange, 147 mm x 223 mm x 15 mm	TZ106	1	piece
2CPX010460R9999	Flange, 147 mm x 223 mm x 20 mm	TZ107	1	piece
2CPX010850R9999	Flange, 147 mm x 223 mm x 20 mm	TZ110	1	piece
2CPX010851R9999	Flange, 147 mm x 223 mm x 20 mm	TZ111	1	piece
2CPX010852R9999	Flange, 147 mm x 223 mm x 20 mm	TZ112	1	piece
2CPX010487R9999	Enclosure accessories, 70 mm x 100 mm x 180 mm	TZ503	1	piece
2CPX010488R9999	Enclosure accessories, 70 mm x 100 mm x 180 mm	TZ504	1	piece
2CPX010489R9999	Enclosure accessories, 70 mm x 100 mm x 180 mm	TZ505	1	piece
2CPX010490R9999	Enclosure accessories, 70 mm x 100 mm x 180 mm	TZ506	1	piece

2CPX010494R9999	Enclosure accessories, 160 mm x 35 mm x 45 mm	TZ510	1	piece
2CPX010503R9999	Cabinet connection, 25 mm x 150 mm x 240 mm	TZ608	1	piece
2CPX010673R9999	Enclosure accessories, 500 mm x 100 mm x 30 mm	TZ618	1	piece
2CPX010674R9999	Enclosure accessories, 800 mm x 100 mm x 30 mm	TZ619	1	piece
2CPX010778R9999	Cabinet connection, 55 mm x 160 mm x 260 mm	TZ626	1	piece
2CPX010650R9999	Touch guard, 1200 mm x 1000 mm x 30 mm	TZP408	1	piece
2CPX010733R9999	Touch guard, 1200 mm x 1000 mm x 30 mm	TZP408A	1	piece
2CPX038233R9999	Enclosure accessories, 297 mm x 148 mm x 3 mm	ZA13	1	piece
2CPX038228R9999	Enclosure accessories, 210 mm x 148 mm x 3 mm	ZA5	1	piece
2CPX038227R9999	Enclosure accessories, 297 mm x 210 mm x 3 mm	ZA6	1	piece
2CPX038001R9999	Enclosure accessories, 15 mm x 400 mm x 15 mm	ZL8	1	piece
2CPX010799R9999	Enclosure accessories, 30 mm x 20 mm x 100 mm	TZ616A	1	piece
2CPX010999R9999	Enclosure accessories, 30 mm x 20 mm x 100 mm	TZ634A	1	piece
2CPX011000R9999	Enclosure accessories, 30 mm x 20 mm x 100 mm	TZ634	1	piece
2CPX038471R9999	Enclosure accessories, 305 mm x 315 mm x 14 mm	ZA123	1	piece
2CPX038472R9999	Enclosure accessories, 235 mm x 222 mm x 14 mm	ZA125	1	piece
2CPX062381R9999	Enclosure accessories, 297 mm x 210 mm x 3 mm	ZA13P10	1	piece
2CPX062382R9999	Enclosure accessories, 210 mm x 148 mm x 3 mm	ZA5P10	1	piece
2CPX062375R9999	Enclosure accessories, 297 mm x 210 mm x 3 mm	ZA61P10	1	piece
2CPX062380R9999	Enclosure accessories, 297 mm x 210 mm x 3 mm	ZA6P10	1	piece
2CPX060490R9999	Enclosure accessories, 30 mm x 30 mm x 30 mm	ZH130	1	piece
2CPX060491R9999	Enclosure accessories, 16 mm x 16 mm x 18 mm	ZH131	1	piece
2CPX060492R9999	Enclosure accessories, 25 mm x 25 mm x 35 mm	ZH132	1	piece
2CPX060493R9999	Enclosure accessories, 25 mm x 25 mm x 45 mm	ZH133	1	piece
2CPX060494R9999	Enclosure accessories, 15 mm x 15 mm x 20 mm	ZH134	1	piece
2CPX060495R9999	Enclosure accessories, 15 mm x 15 mm x 25 mm	ZH135	1	piece
2CPX060496R9999	Enclosure accessories, 15 mm x 15 mm x 20 mm	ZH136	1	piece
2CPX060497R9999	Enclosure accessories, 20 mm x 20 mm x 30 mm	ZH137	1	piece
2CPX060502R9999	Enclosure accessories, 15 mm x 30 mm x 35 mm	ZH142	1	piece
2CPX060657R9999	Enclosure accessories, 50 mm x 80 mm x 15 mm	ZH157	1	piece
2CPX060658R9999	Enclosure accessories, 50 mm x 80 mm x 15 mm	ZH158	1	piece
2CPX060660R9999	Enclosure accessories, 50 mm x 80 mm x 15 mm	ZH160	1	piece

2CPX060661R9999	Enclosure accessories, 50 mm x 80 mm x 15 mm	ZH161	1	piece
2CPX060662R9999	Enclosure accessories, 50 mm x 80 mm x 15 mm	ZH162	1	piece
2CPX060663R9999	Enclosure accessories, 50 mm x 80 mm x 15 mm	ZH163	1	piece
2CPX060664R9999	Enclosure accessories, 50 mm x 80 mm x 15 mm	ZH164	1	piece
2CPX060665R9999	Enclosure accessories, 50 mm x 80 mm x 15 mm	ZH165	1	piece
2CPX066091R9999	Enclosure accessories, 75 mm x 75 mm x 15 mm	ZH91	1	piece
2CPX010451R9999	Flange, 147 mm x 223 mm x 20 mm	TZ101P10	1	piece
2CPX010826R9999	Flange, 147 mm x 223 mm x 20 mm	TZ101P100	1	piece
2CPX010453R9999	Flange, 147 mm x 223 mm x 20 mm	TZ102P10	1	piece
2CPX010455R9999	Flange, 147 mm x 223 mm x 20 mm	TZ103P10	1	piece
2CPX010932R9999	Flange, 147 mm x 223 mm x 20 mm	TZ104P10	1	piece
2CPX010933R9999	Flange, 147 mm x 223 mm x 20 mm	TZ105P10	1	piece
2CPX010459R9999	Flange, 147 mm x 223 mm x 15 mm	TZ106P10	1	piece
2CPX010461R9999	Flange, 147 mm x 223 mm x 20 mm	TZ107P10	1	piece
2CPX010934R9999	Flange, 147 mm x 223 mm x 20 mm	TZ110P10	1	piece
2CPX010935R9999	Flange, 147 mm x 223 mm x 20 mm	TZ111P10	1	piece
2CPX046613R9999	Flange, 75 mm x 75 mm x 68 mm	RZF10	1	piece
2CPX046612R9999	Flange, 58 mm x 58 mm x 54 mm	RZF9	1	piece
2CPX010782R9999	Enclosure accessories, 30 mm x 65 mm x 45 mm	TZ604	1	piece
2CPX010790R9999	Enclosure accessories, 30 mm x 65 mm x 45 mm	TZ604A	1	piece
2CPX010820R9999	Enclosure accessories, 30 mm x 65 mm x 45 mm	TZ604P10	1	piece
2CPX010821R9999	Enclosure accessories, 30 mm x 65 mm x 45 mm	TZ604P100	1	piece
2CPX010783R9999	Enclosure accessories, 30 mm x 40 mm x 45 mm	TZ605	1	piece
2CPX010791R9999	Enclosure accessories, 30 mm x 40 mm x 45 mm	TZ605A	1	piece
2CPX010822R9999	Enclosure accessories, 30 mm x 40 mm x 45 mm	TZ605P10	1	piece
2CPX010823R9999	Enclosure accessories, 30 mm x 40 mm x 45 mm	TZ605P100	1	piece
2CPX010784R9999	Enclosure accessories, 20 mm x 80 mm x 20 mm	TZ606	1	piece
2CPX010792R9999	Enclosure accessories, 20 mm x 80 mm x 20 mm	TZ606A	1	piece
2CPX010824R9999	Enclosure accessories, 30 mm x 80 mm x 20 mm	TZ606P10	1	piece
2CPX010825R9999	Enclosure accessories, 30 mm x 80 mm x 20 mm	TZ606P100	1	piece
2CPX010972R9999	Enclosure accessories, 28 mm x 30 mm x 350 mm, Isolated (Class II), IP20	TZ650	1	piece
2CPX010779R9999	Enclosure accessories, 18 mm x 22 mm x 24 mm	TZ601	1	piece
2CPX010787R9999	Enclosure accessories, 18 mm x 22 mm x 24 mm	TZ601A	1	piece
2CPX010814R9999	Enclosure accessories, 18 mm x 22 mm x 24 mm	TZ601P10	1	piece
2CPX010815R9999	Enclosure accessories, 18 mm x 22 mm x 24 mm	TZ601P100	1	piece
2CPX010616R9999	Mounting plate, 1200 mm x 996 mm x 2 mm	TZM408	1	piece

2CPX010766R9999	Mounting plate, 1200 mm x 996 mm x 2 mm	TZM408A	1	piece
2CPX010800R9999	Enclosure accessories, 500 mm x 100 mm x 30 mm	TZ618A	1	piece
2CPX010801R9999	Enclosure accessories, 800 mm x 100 mm x 30 mm	TZ619A	1	piece
2CPX062335R9999	Interior fitting system, 33 mm x 38 mm x 16 mm	ED44P10	1	piece
2CPX062703R9999	Interior fitting system, 33 mm x 38 mm x 16 mm	ED44P1000	1	piece
2CPX062308R9999	Interior fitting system, 33 mm x 38 mm x 16 mm	ED44P50	1	piece
2CPX062336R9999	Interior fitting system, 55 mm x 47 mm x 16 mm	ED45P10	1	piece
2CPX062704R9999	Interior fitting system, 55 mm x 47 mm x 16 mm	ED45P1000	1	piece
2CPX062310R9999	Interior fitting system, 55 mm x 47 mm x 16 mm	ED45P50	1	piece
2CPX062384R9999	Enclosure accessories, 55 mm x 215 mm	ZA1P5	1	piece
2CPX062378R9999	Enclosure accessories, 55 mm x 215 mm	ZA1P50	1	piece

分类

低压产品及系统 → 箱壳类产品 → 三相分支配电箱 → Sub Distribution Boards → TwinLine N 55 - Welded

