

## 2005 XL 0221

### Workshop trolley

Code	ETIM
3437515	EC011808
EAN	UNSPSC
4010886971413	56-12-18-02
Country of origin	eCl@ss
Germany	21-07-11-00
Customs tariff number	
94032080	



### Article description

- Body:
  - Storage surface of ABS plastic with small parts compartment
  - Manoeuvrable and easy to steer with drive/steer handle
  - Side walls with Euro perforation 10 x 38 mm for attaching hooks and tools
  - Edge protection to minimize the damage of impacts
  - Sheet steel, corrosion and scratch-resistant, powder-coated, GEDORE blue
- Drawers:
  - Central locking with cylinder lock
  - Wide drawers (W 792 x D 400 mm) with full extension, removable
  - Safety locking per drawer, one-hand operation
  - Guide rails with ball bearings
  - Can be individually equipped with longitudinal and transverse dividers (also available individually)
  - Load capacity per drawer 60 kg, lower heavy-duty drawer 70 kg
  - GEDORE high-performance chassis:
    - Total load capacity 1000 kg static (750 kg dynamic)
    - 2 GEDORE heavy-duty wheels with roller bearings (fixed castors, 200 mm) • 2 GEDORE easy-running wheels with ball bearings (swivel castors, 125 mm), both with total brake each
    - Even under maximum loads, the GEDORE axle design ensures: smooth running, maneuverability and directional stability
  - Accessories:
    - Longitudinal (LT) and transverse dividers (QT) made of galvanized sheet steel (also available individually)
  - Options:
    - Can be optimally equipped with GEDORE tool modules (No. 1500 ES/1500 CT or 2005 CT)

### Article information

Contents (Qty of pieces)	1	Number of lengthwise dividers	3
Net weight [kg]	92 kg	Number of drawers	5
Total length [mm]	1.021 mm	Load capacity per drawer [kg]	60 kg
Total width [mm]	605 mm	Fixed roller diameter (2x)	200
Total height [mm]	1.020 mm	Swivel castor diameter with brakes (2x)	125
Surface	powder-coated	Single pull-out stop	no
Total depth [mm]	605 mm	Number of wheels	4
Material	Sheet steel	Static load carrying capacity [kg]	1000 kg
Colour	GEDORE blue, RAL 5017	Load capacity heavy duty drawer [kg]	70 kg
Load capacity kg	750 kg	Type of closure	Zentralverriegelung
Number of crosswise dividers	2		