

**Part Number :** [191150007](#)

**Product Description :** Avikrimp Snap Spade


Terminal for 22-18 AWG Wire

**Series Number :** 19115

**Status :** Active

**Product Category :** Ring and Spade Terminals

**Engineering Number :** AA-8704-05



---

## Documents & Resources

### Drawings

[191150007\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[PS-19902-013-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Ring and Spade Terminals
Series	19115
Description	Avikrimp Snap Spade Terminal for 22-18 AWG Wire
Keyword	Spade Terminal, Spade Terminals
Product Name	Avikrimp
Style	Spade Snap
Type	Spade Connector
UPC	800753091832

### Agency

CSA	LR18689
UL	E32244

### Physical

Barrel Type	Closed
Flammability	94V-2
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Net Weight	0.730/g
Packaging Type	Bag
Plating min - Mating	4.064µm

Plating min - Termination	4.064µm
Stud Size	5 (M3)
Wire Insulation Diameter	3.60mm max.
Wire Size (AWG)	18, 20, 22

---

## Application Tooling

### Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 22-10 AWG and 6.0-0.5mm <sup>2</sup> (Rings, Spades, Hooks, Block Spades and Flanged Spades)	<u>640010100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640050100</u>
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	<u>640160036</u>