

Chemical-resistant CSM gloves, offering lasting hand protection

Port size: 203mm/8"

Thickness: 0.4mm/16 mil

- **Specialized defenses:** The AlphaTec® CSM Isolator Glove 85-300 offers excellent chemical resistance, protecting wearers against concentrated acids and bases
- **Elevated comfort:** These CSM gloves are made from soft, flexible material, for everyday comfort and usability
- **Prolonged glove life:** The AlphaTec® CSM Isolator Glove 85-300 can also withstand prolonged exposure to oxygen, UV rays and ozone without rapidly aging, and they boast EN 388:2016+A1:2018 Level 3 abrasion resistance
- **Reduced contamination risks:** These PPE gloves are white in color, facilitating contamination detection



KEY FEATURES & BENEFITS

- **Robust CSM composition:** Resistant against concentrated acids/bases
- **Flexible material:** For comfortable, easy-to-use safety gloves
- **Durable design:** Withstands prolonged oxygen, UV ray and ozone exposure

TECHNICAL DATA SHEET

Product Reference	85-300
Material	Chlorosulfonated polyethylene_CSM
Color	White
Shape	Ambidextrous
External Glove Surface	Smooth
Cuff Style	Beaded
Storage Instructions	Store in a dry and dark environment, temperature of 5°C to 22°C. Retain in original packaging when not in use.
Available Sizes	11, 9.5
Temperature Range	From -20°C to 120°C
Shelf Life	Three (3) years from date of manufacture.
Standards	CE 0493, EN 388:2016 +A1:2018, EN ISO 21420:2020, EN ISO 374-5:2016, EN ISO 374-1:2016 Type B, Category III
Vulcanization Chemical Accelerators	None

PHYSICAL PROPERTIES

	Typical Values	Testing Method
Typical Length (mm/in)	800/32	EN ISO 21420
Port Size	203mm/8"	
Target Single Wall Palm Thickness (mm/mil)	0.4 /16	EN 455-2
Target Single Wall Cuff Thickness (mm/mil)	0.4 / 16	EN 455-2

PROTECTION AGAINST MECHANICAL RISKS, EN 388:2016+A1:2018

Risk	Performance level
Abrasion Resistance	Level 3
Blade Cut Resistance	Level 1
Tear Resistance	Level 0
Puncture Resistance	Level 1

ORDERING INFORMATION

	PORT SIZE	8"/203mm	8"/203mm
	SIZE	9.5	11
85-300	REORDER NO.	85300095	85300110

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
US T: +1 800 800 0444
US F: +1 800 800 0445
CA T: +1-800-363-8340

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

UK

Ansell Nitritex
T: +44 1638 663338
F: +44 1638 668890

Performance Standards and Regulatory Compliance



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.