

## DWD024K-QS

650W Hammer Drill

**DEWALT**

5035048268186

### Product Description:

No-load speed (rpm): 0-2800 Striking rate (cps/min): 0-47600 Ø Wood/metal/concrete drilling (mm): 25/13/16 Chuck capacity (mm): 1.5-13



### Product features and benefits:

- Variable speed control at the trigger to allow the user to drill progressively for greater precision Locking device to ensure constant speed for applications requiring repetitive tasks Compact design that ensures user comfort and access to
- Very narrow spaces Very low weight to ensure true comfort through
- simplicity and a strong reduction in fatigue in use The qualities of this tool are its excellent power/weight ratio, its performance, its reliability
- and its compactness Soft grip handle that considerably improves the comfort of use
- 

### Specifications techniques :

- Output power: 302 W
- Power supply: 710 W
- Chuck Capacity: 1.5-13 mm
  - Drilling capacity (wood): 25 mm
  - Drilling capacity (metal): 13 mm Capacity
  - Drilling (masonry): 16 mm Maximum torque: 5.2 Nm

### Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

### Included Items:

- High-quality carrying case (x1)
- Depth stop (x1)
- Multi-position side handle (x1)
- Keyed chuck (x1)

