

FEATURES

- **Sintered Bronze Material:** Provides excellent wear resistance and durability.
- **Flanged Design:** Ensures secure and precise positioning in assemblies.
- **Bore Size of 20.02 mm:** Suitable for a wide range of shafts and applications.
- **Outside Diameter of 26.05 mm:** Fits standard housings for easy installation.
- **Width of 25 mm:** Offers stability and support in dynamic applications.
- **Dynamic Load Rating of 14 N/mm²:** Handles moderate dynamic loads effectively.
- **Static Load Rating of 50 N/mm²:** Capable of supporting high static loads.

RS PRO 20.02 mm Flanged Plain Bearing

RS Stock No: 518-246



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price

Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable and efficient rotational movement. Made from sintered bronze, it offers excellent durability and performance in various industrial settings. The flanged design ensures secure positioning, making it ideal for use in machinery and equipment where precise alignment is crucial.

General Specifications

Bore Size	20.02 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	26.05 mm
Width	25 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------