

10 ft Black USB 2.0 Extension Cable A to A - M/F

Product ID: USBEXTAA10BK



The USBEXTAA10BK 10-foot USB Extension Cable (A-A) features 1 USB A male connector and 1 USB A female connector, extending the connection between USB 2.0 devices by up to 10 feet - an ideal solution for better placement of peripheral devices, or adding flexibility to existing USB ports.

This high quality USB extension cable is fully rated for use with USB 1.1 and USB 2.0 devices, and is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Extend your USB connection to connect a USB printer or any USB peripheral device to a PC or Mac at high-performance data transfer speed

Features

- Designed and constructed to USB 2.0 specifications
- Molded strain relief
- Supports data transfer rates up to 480 Mbps

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
Performance	Type and Rate	USB 2.0 - 480 Mbit/s
Connector(s)	Connector A	1 - USB Type-A (4 pin) USB 2.0 Male
	Connector B	1 - USB Type-A (4 pin) USB 2.0 Female
Physical Characteristics	Cable Length	3 m [10 ft]
	Color	Black
	Product Length	3 m [10 ft]
	Weight of Product	96 g [3.4 oz]
	Wire Gauge	24/28 AWG
Packaging Information	Package Height	15 mm [0.6 in]
	Package Length	22.5 cm [8.9 in]
	Package Width	12.5 cm [4.9 in]
	Shipping (Package) Weight	101 g [3.6 oz]
What's in the Box	Included in Package	1 - 10 ft Black USB 2.0 Extension Cable A to A - M/F

Product appearance and specifications are subject to change without notice.