

General Information

Extended Product Type:	463RU6
Product ID:	2CMA167532R1000
EAN:	7392696675321
Catalog Description:	Socket-outlet, panel mounting, 6h, 63A, IP44, unified flange, straight, 3P+N+E
Long Description:	Socket-outlet, panel mounting, earthing sleeve position 6h, rated current 63A, IP44 splash proof, unified flange, straight, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red

Additional Information

Additional Information:	3P+N+E
Cable Cross-Section:	6 ... 25 mm ²
Color:	Red
Country of Origin:	Czech Republic (CZ)
Customs Tariff Number:	85366990
Data Sheet, Technical Information:	2CMC700014C0008
Declaration:	2CMC700005D0001
Declaration of Conformity - CE:	2CMC700005D0001
Degree of Protection:	IP44
E-nummer:	2416680
EAN:	7392696675321
ETIM 4:	EC001317 - Panel-mounted CEE socket outlet
ETIM 5:	EC001321 - CEE socket outlet
ETIM 6:	EC001321 - CEE socket outlet
Enclosure Material:	Thermoplastic polyester (PBT)
Environmental Information:	2CMC700001D0002
Frequency (f):	60 Hz
Function:	Socket outlet, panel mounting, unified flange, straight
Gross Weight:	0.7 kg
Housing Material:	Thermoplastic (PBT)
IIT Publishing Status:	Level 0 - Information enabled
Instructions and Manuals:	2CMC700002D0001
Invoice Description:	Ind. P&S#463RU6
Minimum Order Quantity:	1 piece
Mounting Type:	unified flange, straight
Number of Poles:	5
Object Classification Code:	2CMT005069
Package Level 1 EAN:	7392696675321
Package Level 1 Gross Weight:	0.7 kg
Package Level 1 Height:	139 mm
Package Level 1 Length:	112 mm
Package Level 1 Units:	1 piece
Package Level 1 Width:	112 mm
Product Main Type:	TRU
Product Name:	Industrial Socket Outlet Panel Mounting
Product Net Depth:	135 mm
Product Net Height:	135 mm

Product Net Length:	112 mm
Product Net Weight:	0.653 kg
Product Net Width:	100 mm
Protection Type:	Splashproof
Rated Current (I_n):	63 A
Rated Voltage (U_r):	200/346 ... 240/415 V
RoHS Date:	L23
RoHS Information:	2CMC700057D0001
RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
Selling Unit of Measure:	piece
Short Description:	Socket-outlet, panel mounting, 6h, 63A, IP44, unified flange, straight, 3P+N+E
Size:	135X100X100
Standards:	IEC 60309-1 IEC 60309-2
Suitable For:	Socket Outlets for Panel Mounting
Suitable for Product Class:	Industrial Plugs and Sockets
UNSPSC:	39120000
Clock Position Of Grounding Contact:	6 hour