




Datasheet

Product Name:	MIL-W-16878/5 26AWG
Product Discription:	MIL-W-16878/5 26AWG
Specification No.:	
Customer's Name:	

Description					Construction					
Rated Voltage:	1000V				Conductor	Stranded Sliver plated copper				
Rated Temperature:	200°C				Size(AWG)	26				
Reference Standard:	MIL-W-16878/5				Construction(±0.008mm)	19/0.10				
Cross Section					Stranded Dia.(mm)Ref.	0.5				
					Insulation Material	PTFE				
					Insulation Color	ANY COLOR				
					Ave Thickness(mm)	0.38				
					Insulation Dia.(±0.08mm)	1.26				
Marking					Remark:					
No marking on the cable jacket					8775465 Red 8775456 Blue 8775459 Black 8775468 White 8775452 Brown					
Applications					Characteristics					Customer Approve
These wires are ideal for internal wiring of appliances, electronic equipment and other applications.					Test Item	Standard Value				Seal & Stamp
					Test Material	PTFE(ROHS)				
					Insulation resistance(20°C MΩ*m)	1000				
					Vol. Tesr(AC.V.60S) (V)	2000				
					Flammability Test	VW-1				
					Max.DC Resistance(20°C Ω/km)	122.37(MAX)				
Revisions										Signature: Date:
Version	Description	Drawn by	Approved by	Date						
0	New document issue	Danniel	Jason	19/05/2015						