## Product data sheet Characteristics

## A9S60463

# switch Acti9 iSW - 4 poles - 63A - 415V



Main	
Product or component type	Switch disconnector
Range of product	ISW
Device short name	ISW
Switch application	Isolation Control
Poles description	4P
Utilisation category	AC-22A conforming to EN 60947-3 AC-22A conforming to IEC 60947-3
Suitability for isolation	Yes conforming to EN 60947-3 Yes conforming to IEC 60947-3

### Complementary

[le] rated operational current	63 A AC 50/60 Hz 415 V	
[Ue] rated operational voltage	415 V AC 50/60 Hz	
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to IEC 60947-3	
[Uimp] rated impulse withstand voltage	6 kV conforming to EN 60947-3 6 kV conforming to IEC 60947-3	
Control type	Toggle	
Local signalling	ON/OFF indication	
Contact position indicator	Yes	
Mounting mode	Fixed	
Mounting support	35 mm symmetrical DIN rail	
Comb busbar distribution block compatibility	Standard	
9 mm pitches	8	
Colour	White	
Mechanical durability	50000 cycles	
Electrical durability	20000 cycles	
Connections - terminals	Tunnel type terminals 1 cable(s) 635 mm² flexible Tunnel type terminals 1 cable(s) 650 mm² rigid	

#### **Environment**

Standards	IEC 60947-3	
IP degree of protection	IP4	
Pollution degree	3 conforming to IEC 60947-3	
RoHS EUR status	Compliant	
RoHS EUR conformity date	1001	