

Portable fan heaters

For fast heat up over a localised area, these Dimplex fan heaters suit all needs.

Most feature:

- Choice of heat settings
- Thermostatic control (except MCF15R/B)
- 3 year guarantee (except DXSTG25* and MCF15R/B*)

Look out for advanced features including:

- Motorised oscillation (DXSTG25 and DXUC2LCD)
- Electronic climate control (DXGLO2, DXSTG25 and DXUC2LCD)
- Optiflame® effect (MCF15R/B)
- Unique LED ring-lit technology (DXGLO2)
- Fun Footie (DXDFB2) or Daisy (DXDAI2) motifs

*One year only.



Model DXGLO2

Model Microfire MCF15B



Model Studio G



Model Studio G



Model DXUC2LCD



Model DXUF30T

Model	Loading	Thermostat	Choice of heat settings	Mains neon	Cool blow	Dimensions (H x W x D)	Weight	Colour
Upright fan heaters								
DXUF20T	2kW	Y	Y	Y	Y	238 x 247 x 184mm	1.4kg	Light grey
DXUF30T	3kW	Y	Y	Y	Y	238 x 247 x 184mm	1.4kg	Light grey
DXGLO2	2kW	Y Electronic	Y	Y-LCD	Y	278 x 230 x 158mm	1.5kg	Black
DXUC2LCD	2kW	Y Electronic	Y	Y	Y	274 x 205 x 205mm	2.0kg	White
Studio G DXSTG25	2kW	Y Electronic	Y	Y-LED	N	825 x 263 x 263mm	4.4kg	Black
Microfire MCF15R/B	1.5kW	N	Y	N	N	370 x 330 x 205mm	6.9kg	Red or Black
Flat fan heaters								
DXFF20TSN	2kW	Y	Y	Y	Y	114 x 253 x 245mm	1.2kg	White
DXFF30TSN	3kW	Y	Y	Y	Y	114 x 253 x 245mm	1.2kg	White
Daisy DXDAi2	2kW	Y	Y	Y	Y	114 x 253 x 245mm	1.2kg	Pink
Footie DXDFB2	2kW	Y	Y	Y	Y	114 x 253 x 245mm	1.2kg	White



Model DXFF30TSN



Model Daisy DXDAi2



Model Footie DXDFB2



scan for more info
dimplex.co.uk/fans