

LUMINA

AA20PJI050P41-38X38 TFR

EAN 4031582385632

Swivel castor, housing made of Polypropylene, plate fitting. Wheel centre made of Polypropylene, Tread: TENTEpren (thermoplastic rubber), grey non-marking, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	50 mm
Wheel width	10 mm
Castor width	55 mm
Size of Plate	38 x 38 mm
Plate hole centres	28 x 28 mm
Plate hole	4,4 mm
Swivel Interference	98 mm
Overall height	63 mm
Temperature	- 10 / + 40 °C
Standard	EN_12528
Weight	0.105 kg
Swivel Radius	49 mm
Hardness of tread	Shore A 87
Load capacity	40 kg
Load capacity (static)	80 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○