

Part Number: 2023X22X

Type	Size	Power	Description
Lamp	T18 BA15S	2.5 W	LED Replacement lamp

## T18, BA15S, 3014 x 39 LEDs

Dimensions: mm



Part #	Colour (K)	Voltage (V)*	Nom Current (mA)	Luminous Intensity (Lm)	Life Hrs
20238221	Warm White 2700 – 3000K	10 - 30Vdc	175mA @ 12V	250	30000
20238223	White 6000 – 6500K	10 - 30Vdc	175mA @ 12V	250	30000

### Notes:

- \* This product is not polarity sensitive.
- RoHS and REACH compliant.
- Due to component tolerances, colour temperature variations may be observed.
- Marking: Operational voltage.
- Electrical & optical data are measured at an ambient temperature of 25°C.