

## Han 10A-Cover-Plastic 2 Pins, f. BP



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 010 5410
Specification	Han 10A-Cover-Plastic 2 Pins, f. BP
HARTING eCatalogue	<a href="https://harting.com/09200105410">https://harting.com/09200105410</a>

### Identification

Category	Accessories
Series of hoods/housings	Han A <sup>®</sup>
Type of accessory	Protection cover
Description of the accessory	for bearing pedestal

### Version

Size	10 A
Locking type	Single locking lever

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Thermoplastic
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes



**Pushing Performance**  
Since 1945

## Material properties

California Proposition 65 substances	Nickel Naphthalene
--------------------------------------	-----------------------

## Commercial data

Packaging size	1
Net weight	18.3 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140039537
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467