

## Features

- **Flexible & Durable –** Withstands continuous pressure and adapts to radial shaft movement.
- **High-Temperature Resistance –** Operates effectively in water, steam, and chemicals up to 200°C.
- **Versatile Applications –** Ideal for plungers, centrifugal pumps, and valves.

## RS PRO Gland Packing Type GLP720

**11mm x 8m Length**

RS Stock No.: 0606574



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

### *P720 – High-Performance Acrylic Gland Packing*

*P720 is a high-quality gland packing, meticulously braided from acrylic yarn and mineral oil, with PTFE impregnation for enhanced sealing efficiency and chemical resistance. Its composition ensures excellent flexibility, durability, and lubrication, making it ideal for demanding industrial applications.*

### *Industry Applications:*

*Chemical Processing & Pharmaceuticals – Reliable for aggressive chemical environments. Food & Beverage Industry – Ensures long-lasting, precision sealing.*

*Power & Steam Systems – Effective in high-temperature water and steam applications.*

*Engineered to meet specific industry demands, P720 is the go-to solution for high-performance gland sealing, offering longevity, efficiency, and reliability in critical applications.*

## Specifications

<b>Roll Length</b>	8m
<b>Width</b>	11mm
<b>Thickness</b>	11mm
<b>Colour</b>	White
<b>Material</b>	Polyacrylic (ACM)
<b>Minimum Operating Temperature</b>	-50
<b>Maximum Operating Temperature</b>	200
<b>pH Range</b>	2-12
<b>Velocity (m/s)</b>	10
<b>Maximum Pressure for Rotary Pump (Kpa)</b>	2000
<b>Maximum Pressure for Piston Pump (Kpa)</b>	2000