

# Datasheet

# Stainless Steel Threaded Straight Reducer, 1/4 in R Male, 1/8 G Female

RS Stock number [3108652](#)



## Features

- Reducer Male to Female BSPTM – BSPPF
- Stainless steel construction offers excellent chemical resistance
- Maximum working pressure: 150 bar
- Body: Stainless steel 316L

## Specifications

- Working Temperature: -20 to 180 °C
- Connection 1: 1/4in R Male
- Connection 2: 1/8in G Female
- Connection Gender 1: Male
- Connection Gender 2: Female
- Fitting Direction: Straight
- Fitting Type: Reducer
- Thread Size 1: 1/4in
- Thread Size 2: 1/8in
- Thread Standard 1: R
- Thread Standard 2: G

## Measurements

- C1: R1/4
- C2: G1/8
- F (mm): 14
- L (mm): 16
- Weight (kg): 0.008

