



 PRODUCT-DETAILS

AT21/M20/C90/BLY

90D PA66 FITTING M20 21MM-BLY



General Information

Extended Product Type	AT21/M20/C90/BLY
Product ID	7TCA296170R0256
EAN	5020963037979
Catalog Description	90D PA66 FITTING M20 21MM-BLY
Long Description	Adaptalok ATS, 90 Degree Conduit Fitting, Fixed External Male Thread, Nominal Conduit Size 21mm, M20 Thread, Polyamide (Nylon) 66/TPE, Black with Yellow Elastomer

Additional Information

Product Main Type	Adaptaflex Flexible Cable Protection
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit

Ordering

EAN	5020963037979
UPC	786210282275

Technical

Number of Batteries	0
Color	Black/Yellow Elastomer
Material	Polyamide/Nylon 6.6
Size	NC 21mm

Environmental

WEEE Category	Product Not in WEEE Scope
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units	10 piece
Package Level 1 EAN	5020963037979
Package Level 1 Height	9.84 in 250 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	7.87 in 200 mm

Certificates and Declarations

Declaration of Conformity - CE	9AKK107492A9618
RoHS Declaration	9AKK107992A8994
REACH Declaration	9AKK107992A8994

External Classifications and Standards

ETIM 8	EC001176 - Screw connection for corrugated plastic hose
ETIM 9	EC001176 - Screw connection for corrugated plastic hose
UNSPSC	39121311

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

