

# Wireless outdoor camera

Art. no. TVAC18010B

Page 1 of 2



- Wireless outdoor camera for digital wireless monitoring set
- Simple step-by-step installation with app and QR code (iOS, Android)
- App access of up to 4 cameras
- VGA resolution and infrared night vision function
- Sturdy, weatherproof outdoor cameras (IP66)
- Professional integrated motion detection (PIR sensor) with alarm function
- Integrated motion detection (PIR sensor)

## Sturdy wireless outdoor camera for 24 h safety

This wireless outdoor camera serves as an extension of the digital wireless monitoring set from ABUS. Thanks to the solid, weatherproof design, it is ideal for outdoor areas. The VGA resolution and the infrared night view function ensure optimal video image data quality at any time of day or night. Integrated motion detection with an alarm function reliably detects movement and sets off an alarm if there is danger of unauthorised access.

## Intuitive installation with app or QR code

Installation is done step-by-step using the app or the QR code, making it easy even for technical laymen. The app also allows access to up to four cameras of this type, making practical mobile monitoring possible.

# Wireless outdoor camera

Art. no. TVAC18010B

Page 2 of 2

**Technical Data:**

Dimensions	150 x 74 x 68 mm
Number of IR LEDs	6
Resolution	640 x 480 (VGA)
Image sensor	1/4'' CMOS
Horizontal angle	60
Width	74 mm
Frequency	2.4 GHz
Wireless range	100 m
Height	68 mm
IR cut filter	Yes
Length	150 mm
Max. operating temperature	50

Min. operating temperature	-10
Modulation	GFSK FM / AM
Net weight	0.39 kg
Lens	3,6 mm
Range of night vision function	8 m
IP protection class	66
Transmission power	15 +/- 2 dBm
Sensitivity	-80 dBm
DC voltage supply	5 V
Power consumption	550 mA