Abrasive mop disc

SMT 324 EXTRA





Properties

Grain	Zirconia alumina
Backing plate	Glass fibre
Design	Convex 12°, flat
Aggression	■■■■■□□
Service life	■■■■□□□

Materials

Stainless steel	●
Steel	●

Product benefit

Universal product for edges and surface work on steel and stainless steel - Good removal rate on angle grinders of all performance classes - No glazing, also under low grinding pressure

Applications

- Metal construction
- Locksmith's shop
- Steel construction

Available grits:

16 20 24 30 36 **40** 50 **60** **80** 100 120 150 180 220 240 280 320 360 400 500 600 800 1000 1200 1500 2000 2500 3000

Diameter x Bore in mm	Form	grain	Vmax m/s	Max. RPM	Packing unit/pcs.	Cat. number
115 x 22,23		40	80 m/s	13300 rpm	10	321509
115 x 22,23		60	80 m/s	13300 rpm	10	321511
115 x 22,23		80	80 m/s	13300 rpm	10	321513
115 x 22,23		40	80 m/s	13300 rpm	10	321645
115 x 22,23		60	80 m/s	13300 rpm	10	321647
115 x 22,23		80	80 m/s	13300 rpm	10	321649

Klingspor Schleifsysteme GmbH und Co. KG
Hüttenstraße 36 - 35708 Haiger - Germany
Fon + 49 (0) 2773 922-0 Fax + 49 (0) 2773 922-186
sales@klingspor.de - www.klingspor.de

Diameter x Bore in mm	Form	grain	Vmax m/s	Max. RPM	Packing unit/pcs.	Cat. number
125 x 22,23		40	80 m/s	12250 rpm	10	321510
125 x 22,23		60	80 m/s	12250 rpm	10	321512
125 x 22,23		80	80 m/s	12250 rpm	10	321514
125 x 22,23		40	80 m/s	12250 rpm	10	321646
125 x 22,23		60	80 m/s	12250 rpm	10	321648
125 x 22,23		80	80 m/s	12250 rpm	10	321650

Klingspor Schleifsysteme GmbH und Co. KG
Hüttenstraße 36 - 35708 Haiger - Germany
Fon + 49 (0) 2773 922-0 Fax + 49 (0) 2773 922-186
sales@klingspor.de - www.klingspor.de