

Han TC70-HMC-MC-CRT-16mm²-AU



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 200 6132
Specification	Han TC70-HMC-MC-CRT-16mm²-AU
HARTING eCatalogue	https://harting.com/09112006132

Identification

Category	Contacts
Series	TC 70
Type of contact	Crimp contact

Version

Termination method	Crimp termination
Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	16 mm²
Rated current	≤70 A
Contact resistance	≤0.3 mΩ
Stripping length	15.5 mm
Limiting temperature	-40 ... +125 °C
Mating cycles	≥10,000
Note on the mating cycles	Mating cycles with other HMC components
Vibration resistance	Category 2 acc. to IEC 61373
Shock resistance	Category 2 acc. to IEC 61373

Material properties

Material (contacts)	Copper alloy
---------------------	--------------



Pushing Performance
Since 1945

Material properties

Surface (contacts)	HMC gold plated
--------------------	-----------------

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	10
Net weight	10.5 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140188143
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522