

ABUS Security-Center



Security Tech Germany

ABUS Wired Outdoor Sounder (orange)

Art.-Nr. AZSG10005

- Rugged, weatherproof outdoor siren
 - Sound pressure 110 dB(A) @ 1 m
 - Adjustable siren duration and volume
 - LED flasher technology
 - Flasher can be mounted on top or bottom
 - Protection class: IP43
-

ABUS Wired Outdoor Sounder (orange)

Art.-Nr. AZSG10005

Dimensions	(WxHxD) mm
Gross weight	1,035 kg
Height	277 mm
Housing material	ABS
Illuminant	LED
Length	75 mm
Luminous color	Orange
Net weight	1,26 kg
Scope of delivery 01 description	Wired outdoor sounder
Scope of delivery 01 quantity	1
Scope of delivery 02 description	Sticker
Scope of delivery 02 quantity	1
Scope of delivery 03 description	Mounting material
Scope of delivery 03 quantity	1
Scope of delivery 04 description	Quick Guide
Scope of delivery 04 quantity	1
Tamper monitoring	Yes
Voltage monitoring	Yes
Width	210 mm