



Main/Emergency-Off Switch - 3, 4, 6 & 8 Pole 20A - 315A



- IP66/67 protection.
- red/yellow padlockable handle.
- optional black handle available.
- insulated enclosure, grey, RAL7035.
- earth terminal included.
- switch interlocked with lid to prevent opening in 'ON' position.

Without Auxiliaries	le AC-21A	3 Pole		Encl. Ref	Price (£)	3 Pole + Solid Neutral (TP&N)		Encl. Ref	Price (£)
	20A	KG10	T203/GBA270 *KS1V	KSAV	21.26	KG10	T203/GBA355 *KS1V	KSAV	22.69
	25A	KG20	T203/GBA270 *KS1V	KSAV	23.85	KG20	T203/GBA355 *KS1V	KSAV	25.45
	32A	KG32	T203/GBA270 *KS1V	KSAV	27.51	KG32	T203/GBA355 *KS1V	KSAV	29.13
	40A	KG41	T203/GBA270 *KL1V	KLCV	42.16	KG41	T203/GBA355 *KL1V	KLCV	43.91
	63A	KG64	T203/GBA270 *KL1V	KLCV	49.31	KG64	T203/GBA355 *KL1V	KLCV	51.08
	80A	KG80	T203/GBA270 *KL1V	KLDV	81.85	KG80	T203/GBA355 *KL1V	KLDV	85.70
	100A	KG100	T203/GBA270 *KL1V	KLDV	92.99	KG100	T203/GBA355 *KL1V	KLDV	96.79
	125A	KG105	T203/GBA270 *KL1V	KLDV	162.73	KG105	T203/GBA355 *KL1V	KLDV	171.75
	125A ³⁾	KG125	T203/GBA270 *ST	ST3	326.66	KG125	T207/GBA355 *ST	ST3	346.96
160A	KG160	T203/GBA270 *ST	ST3	353.53	KG160	T207/GBA355 *ST	ST3	373.83	
200A	KG210	T203/GBA270 *ST	ST3	374.89	KG210	T207/GBA355 *ST	ST4	527.88	
250A	KG250	T203/GBA270 *ST	ST3	388.10	KG250	T207/GBA355 *ST	ST4	540.99	
315A	KG315	T203/GBA270 *ST	ST3	435.07	KG315	T207/GBA355 *ST	ST4	588.41	

With Auxiliaries ¹	le AC-21A	3 Pole		Encl. Ref	Price (£)	3 Pole + Solid Neutral (TP&N)		Encl. Ref	Price (£)
	20A	KG10	T203/GBA281 *KS1V	KSAV	26.35	KG10	T203/GBA374 *KS1V	KSAV	28.09
	25A	KG20	T203/GBA280 *KS1V	KSAV	34.71	KG20	T203/GBA373 *KS1V	KSAV	36.58
	32A	KG32	T203/GBA280 *KS1V	KSAV	38.03	KG32	T203/GBA373 *KS1V	KSAV	39.86
	40A	KG41	T203/GBA280 *KL1V	KLCV	49.77	KG41	T203/GBA373 *KL1V	KLCV	51.54
	63A	KG64	T203/GBA280 *KL1V	KLCV	55.66	KG64	T203/GBA373 *KL1V	KLCV	57.41
	80A	KG80	T203/GBA280 *KL1V	KLDV	90.69	KG80	T203/GBA373 *KL1V	KLDV	96.92
	100A	KG100	T203/GBA280 *KL1V	KLDV	101.83	KG100	T203/GBA373 *KL1V	KLDV	108.02
	125A	KG105	T203/GBA280 *KL1V	KLDV	178.20	KG105	T203/GBA373 *KL1V	KLDV	187.30
	125A ³⁾	KG125	T203/GBA065 *ST	ST3	339.51	KG125	T207/GBA110 *ST	ST3	360.14
160A	KG160	T203/GBA065 *ST	ST3	366.37	KG160	T207/GBA110 *ST	ST3	387.01	
200A	KG210	T203/GBA070 *ST	ST3	396.31	KG210	T207/GBA120 *ST	ST4	549.30	
250A	KG250	T203/GBA070 *ST	ST3	409.53	KG250	T207/GBA120 *ST	ST4	562.41	
315A	KG315	T203/GBA070 *ST	ST3	456.50	KG315	T207/GBA120 *ST	ST4	609.83	

Notes

- 1) The following auxiliary contacts are provided:-
 KG10 1 N.O. (early break) + 1 N.C.
 KG20 to KG105 2 N.O. (early break)
 KG125 to KG315 2 N.O. (early break) + 2 N.C.

2) Switched neutral pole is early make / late break.

3) KG125 suitable for applications requiring larger cable termination and increased enclosure size.