



Main

Range	Acti9
Product or component type	Pan assembly
Device application	Distribution

Complementary

[In] rated current	250 A
Incomer device	Switch disconnecter - 3P Terminal block - 3P MCCB - 3P
Protection device type	Miniature circuit breaker (MCB) 63 A max Residual current circuit breaker with overcurrent protection (RCBO) 45 A max Residual current circuit breaker with overcurrent protection (RCBO PoN) 45 A-max
[Icw] rated short-time withstand current	16 KA
Number of ways	4 ways - 3P + N
Height	130 Mm
Width	375 Mm
Depth	94 Mm
Length	108 Mm
Busbar pitch	18 Mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.0 Cm
Package 1 Width	20.0 Cm
Package 1 Length	29.0 Cm
Package 1 Weight	1.046 Kg

Environmental data

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
RoHS exemption information	Yes

China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product
Take-back	No

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	Commercialised
-----------------------	----------------