

M12-Terminating plug for deviceNet



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 030 1400
Specification	M12-Terminating plug for deviceNet
HARTING eCatalogue	https://harting.com/21030301400

Identification

Category	Accessories
Series	Circular connectors M12
Type of accessory	Termination resistor

Version

Gender	Male
Number of contacts	5
Coding	A-coding

Technical characteristics

Rated current	4 A
Rated voltage	60 V
Limiting temperature	-25 ... +85 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP67 mated condition

Material properties

Material (insert)	Polyamide (PA)
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
Material (hood/housing)	Thermoplastic polyurethane (TPU)
Material flammability class acc. to UL 94	V-0
RoHS	compliant



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	IEC 61076-2-101
----------------	-----------------

Commercial data

Packaging size	1
Net weight	15.3 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140236592
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400