

Technical sheet

CAI309NB

Stainless steel wire rope- 7x19 - AISI 316 - spool-Ø 3 / L 100M





Customs code	7312102000
EAN	3321369977336

Color : Grey

Material : Stainless steel 316

Specifications :

- A high resistance stainless steel 316 cable.
- It's weather-resistant and corrosion-resistant.
- It's of the aviation type with a metal core and a 7 x 19 construction, meaning it consists of 7 strands, each with 19 braided wires.
- Perfect for both indoor and outdoor use.
- This versatile steel cable can be used for various purposes like making nets, guardrails, stair ramps, fences, and more.

Length (m)	Diameter (mm)	Working load (kg)	Net weight (kg)
100	3	135	3,33

VISO
www.viso-cpn.com

VISO - 7 avenue Arago - ZI de la Vigne aux Loups - 91380 CHILLY-MAZARIN - France
Tél. + 33 (0)1 69 53 46 70 - Fax + 33 (0)1 69 53 46 80 - contact@viso-cpn.com / commande@viso-cpn.com