












22POS(X-KEY): I-1827872-1

26POS(X-KEY): I-1827872-3

28POS(X-KEY): I-1827872-4

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm

1. PLG ±

2. PLG ±

3. PLG ±

4. PLG ±

ANGLES ±

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

T. KUDO

D. MITSUGI

D. MITSUGI

108-78268

114-5377

-

16MAR2005

23AUG2005

23AUG2005

tyco Electronics

Tyco Electronics AMP K.K.

Kawasaki, Japan

DYNAMIC D1100D 2.0mmPITCH HDR ASSY (V-TYPE) 22-40POS

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

1827872

-

SCALE

4:1

SHEET

2

OF

3

REV

A1







THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
J	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1 OF 3			



32POS(X-KEY): I-1827872-6

34POS(X-KEY): I-1827872-7

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm

MATERIAL

-

TOO MANY UNLESS OTHERWISE SPECIFIED:

1. PLC ± -

2. PLC ± -

3. PLC ± -

4. PLC ± -

ANGLES ± -

FINISH

DWN: T. KUDO 16MAR2005

CHK: D. MITSUGI 23AUG2005

APVD: D. MITSUGI 23AUG2005

PRODUCT SPEC: 108-78268

APPLICATION SPEC: 114-5377

WEIGHT: -

CUSTOMER DRAWING

Tyco Electronics AMP K.K. Kawasaki, Japan

NAME: DYNAMIC D1100D 2.0mmPITCH HDR ASSY (V-TYPE) 22-40POS

SIZE: A2 CAGE CODE: 00779 DRAWING NO: 1827872 RESTRICTED TO: -

SCALE: 4:1 SHEET: 3 OF 3 REV: A1