



ENGLISH

Datasheet

Stock No. 161-7268

RS PRO Vertical PDU 12 BS Socket Right 3 m BS Plug



BS1363 13 A plug



SPECIFICATIONS:

Product Name: Designated Power Distribution Unit for Cabinet

Socket Type: BS1363 45 degree

Socket Quantity: 12

Power Input: Left end single input

Bracket Install: Inverse installation

Cable with plug: BS1363 13 A plug

Control Function: No controlling function

Protection Function: 2017 hot swaps module

Case: Black

Cable Specification: 3 x 1.5 mm² x 3 M

Product Size: L x W x H = 1092 x 44.4 x 62 mm

Mounting Length: 1066 mm

Case Length: 1036 mm

Fittings: 2 pcs $\phi 6 \times 16$ mm cross bolt, 2 pcs M6 float nut, PDU manual, 1 pc 155 mm cover plate

Electrical Characteristics:

Rating voltage: 250 V ac 50/60 Hz

Rating Current: 13 A

Max. Power: 3250 W

Safety Authentication: CE

Operating Temperature: 0 - 50°C, relative humidity 0 - 95%

Applications:

PDU - Power Distribution Unit is widely used in network enclosure and server rack of data center in field of information technology, telecom, electric, power, finance and insurance, aviation, transportation, hospital, education, E-government etc.