

**BOSCH**

Invented for life

# Product data sheet

## Power tools for trade & industry

Cordless Band Saw

### PRO GCB 18V-63



Bosch's most ergonomic and compact band saw for comfortable working

#### The most important data

|                      |         |
|----------------------|---------|
| Battery voltage      | 18.0 V  |
| Max. cutting depth   | 63.5 mm |
| Weight excl. battery | 3.3 kg  |

**Part Number** 0 601 2A0 401

## Technical data

### Technical data

|  |                      |
|--|----------------------|
| No-load speed                                  | 162 m/min            |
| Saw blade dimensions                           | 733 x 12.7 x 0.35 mm |
| Max. cutting depth                             | 63.5 mm              |
| Weight excl. battery                           | 3.3 kg               |
| Battery voltage                                | 18.0 V               |
| Packaging dimensions (width x length x height) | 360 x 443 x 256 mm   |
| Weight incl. battery                           | 4.3 kg               |

## Noise/vibration information

### Sawing metal

|                             |                      |
|-----------------------------|----------------------|
| Vibration emission value ah | 5.3 m/s <sup>2</sup> |
| Uncertainty K               | 1.5 m/s <sup>2</sup> |



**BOSCH**

Invented for life

# Product data sheet

Power tools for trade & industry

## Advantages:

- Bosch's most ergonomic and compact cordless 18V band saw for comfortable working
- Tool-free blade change via blade tension release and protective guard with metal clips
- Vibration-free blade action and LED light for convenient working



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

