



Part Number : [16021124](#)
Product Description : SL Crimp Terminal, Series 71851, Female, with 0.38µm Selective Gold (Au) Plated Contact, 24-22 AWG, Reel
Series Number : 71851
Status : Active
Product Category : Crimp Terminals
Engineering Number : 71851-0024
Packaging Alternative : [16021125](#) (Bag)



Documents & Resources

Drawings


- [016021124 sd.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Specifications

- [PS-70400-001.pdf](#)
- [PS-71851-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

- [Compliance Statements](#)
- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	71851
Description	SL Crimp Terminal, Series 71851, Female, with 0.38µm Selective Gold (Au) Plated Contact, 24-22 AWG, Reel
Application	Signal, Wire-to-Board, Wire-to-Wire
Product Name	SL
UPC	800753595446

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.062/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	1.905µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.63mm max.

Wire Size (AWG)	22, 24
Wire Size mm ²	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Insertion Tool for 70021,70028, 70110, 71851 Terminals / Extraction Tool for 91821 Terminals	<u>11020022</u>
PremiumGrade Hand Crimp Tool for SL Crimp Terminals, 24-22 AWG and 36-32 AWG	<u>638118700</u>
FineAdjust Applicator for SL Crimp Terminals, for 24-22 AWG Wire with Insulation Diameter 1.40-1.63mm	<u>639023200</u>
T2 Terminator for Female Crimp Terminal	<u>639123200</u>