

















6600 M/465

Assortment of 36 tools, with hooks without panel

		art.
	066000465	6600 M/465



		mm	N°			mm	N°			mm	N°
332		3-16 mm	6	342A		0-50 mm	2	385		270 mm	2
334		3-20 mm	2	358		1"-1.5"	2	386		10-12 mm	2
336		6-18 mm	3	38CH		1.12	2	395T		10-12 mm	2
338		6-12 mm	2	38A/1		0 6,8 50 mm	2				
340		6-26 mm	2	38A/2		0 1.2" 5/16" 3/8"	2				
342		6-12 mm	2	390C		0 25-40 mm	2				